

Applied

Diamond. Inc

5464 Skylane Boulevard, Suite D, Santa Rosa, CA 95403 Toll Free: 855-EOC-6300 www.eoc-inc.com | info@eoc-inc.com



## DIAMOND DETECTORS—X-RAYS AND CHARGED PARTICLES



The superior properties of diamond have proven to be effective for today's 3rd and 4th generation light sources as well as for detecting minimum ionizing particles in High Energy Physics applications where the detector is exposed to high doses of radiation. Position sensitive diamond detectors meet the precise time-of-flight measurement requirements for heavy ion beams consisting of multiple ion species in Nuclear Physics. The detectors are available in a range of packages, including BMC/SMA and TNC



*Ultra-High Thermal Conductivity..* up to 2000 W/mK

sics.

- Large Band Gap (5.45 eV) for low leakage current
- High Electron Hole Mobility for fast signal response
- Extreme Resistance to Harsh Environments

- Very low leakage currents allow for operation at room temperature
- Extreme radiation tolerance extends life
- Larger active diamond area at lower cost

## Thin Detector-grade Diamond Plates and Assemblies IMPROVED CHARGE COLLECTION



## Single Crystal Diamond Plates and Assemblies

Electronic Grade SC Diamond, < 1 ppb nitrogen Standard size of 4 mm sq Standard Thickness of 50, 100 ,300 and 500 um Typical Metalization of Chromium and Gold, 50 nm and 200 nm Lithography available for patterns and strips

## Polycrystalline Diamond Plates and Assemblies

Electronic Grade Polycrystalline Diamond, < 1 ppb nitrogen Standard size of 10 and 20 mm sq Standard Thickness of 50 and 100 um Typical Metalization of Chromium and Gold, 50 nm and 200 nm Lithography available for patterns and strips